ZONO Technologies™

3343 Peachtree Rd. Suite #180 - 1303 Atlanta, GA 30326

zonotechnologies.com

770-212-9201

ZONO™ SC 2 WD Double Door Cabinet with Drying



YOUR TRUSTED PARTNER IN DISINFECTING* & SANITIZING*

EFFECTIVE The ZONO™ Cabinet disinfects and sanitizes many different surfaces, including

plastics, electronics, metal, and varnished wood; and sanitizes fabrics and other

porous surfaces without using liquid chemicals.

SIMPLE The ZONO™ Cabinet is simple to set up and easy to operate. Place items onto

> the Integrated Mobile Carts and roll them directly into the ZONO™ Cabinet. No user assistance is needed during operation, and in 38 minutes, items are

ready to use immediately, with no rinsing, wiping, or worry.

SAFETY Numerous safety features exist to provide protection during operation: **FEATURES**

• Emergency stop buttons inside and outside Ozone sensors Clear safety glass panel doors Magnetic door lock

 Password protected digital display panel Ozone rated door gaskets

SUSTAINABLE • The ZONO™ uses three cents of electricity per cycle•

• The ZONO™ uses less than one ounce of water per cycle"

KILLS 99.9% OF COMMON VIRUSES* & BACTERIA* IN 38 MINUTES (Tested by Certified Independent Laboratories)

✓ Norovirus

✓ Influenza-A ✓ Respiratory Syncytial Virus (RSV)

✓ Staphylococcus aureus (Staph)

✓ Escherichia coli (E. coli)

✓ Streptococcus pyogenes (S. pyogenes)

✓ Shigella dysenteriae (Shigella)

✓ Salmonella enteritidis (Salmonella)

✓ Methicillin-Resistant Staphylococcus aureus (MRSA) ✓ Pseudomonas aeruginosa (P. aeruginosa)

SPECIFICATIONS

• Ozone and humidity are generated in the airtight cabinet to disinfect and sanitize.

Dry cycle dries apparel and gear without damage.

Exterior meets ASTM C1055 standards. Safe to touch during operation.

Dimensions: 80" H x 52 5/8" W x 31 1/16" D.

Capacity: 58.8 cu ft.

Weight: 284 lbs.

No downtime between cycles.

• Requires NEMA 5-20R 120V Receptacle on Dedicated 20A Circuit.

• Sanitizing Cycle Max Watts: 306

Dry Cycle Max Watts: 1518

• Proudly made in the USA in a U.S. EPA registered facility.



Requires NEMA 5-20R 120V Receptacle on Dedicated 20A Circuit.

EASE OF USE FEATURES

ERGONOMIC The Integrated Mobile Cart System aleviates the need for bending and lifting.

FAST Cycles last only 38 minutes. No delay between cycles. **POWER** No hardwiring, only requires plug-in electrical outlet.

OPERATION Simple operating panel.

GUARANTEE Includes a three-year warranty for parts and labor.

OTHER MODELS AVAILABLE

SC 2 Without optional dying cycle.

SC 2 WH Heat cycle kills lice, bedbugs and their eggs (125°F).

ACCESSORIES

RR 7 7-bin Cart **SD 16** Shoe Drying Cart **HC 3M 48** Helmet Cart **RR 10** 10-bin Cart PC 2M 22 Pad Cart **GC** Garment Cart

4S UC 4-shelf Utility Cart

4S D UC 4-shelf Deep Utility Cart



ZONO Technologies™ www.zonotechnologies.com

_31 1/16["]





