


# ZONO™ SC 2 DD WSL Double Door Double Deep Cabinet



## KILLS 99.9% OF COMMON VIRUSES\* & BACTERIA\* IN 38 MINUTES

- EFFECTIVE** The ZONO™ Cabinet disinfects and sanitizes many different surfaces, including plastics, electronics, metal, and varnished wood; and sanitizes fabrics and other porous surfaces without using liquid chemicals.
- SIMPLE** The ZONO™ Cabinet is simple to set up and easy to operate. Place items onto the Integrated Mobile Carts and roll them directly into the ZONO™ Cabinet. No user assistance is needed during operation, and in 38 minutes, items are ready to use immediately, with no rinsing, wiping, or worry.
- SAFETY FEATURES** Numerous safety features exist to provide protection during operation.
  - Emergency stop buttons inside and outside
  - Clear safety glass panel doors
  - Password protected digital display panel
  - Ozone sensors
  - Magnetic door lock
  - Ozone rated door gaskets
- SUSTAINABLE**
  - The ZONO™ uses three cents of electricity per cycle
  - The ZONO™ uses less than one ounce of water per cycle\*\*

## VIRUSES & BACTERIA TESTED & CERTIFIED

- ✓ Norovirus
- ✓ Influenza-A
- ✓ Respiratory Syncytial Virus (RSV)
- ✓ Staphylococcus aureus (Staph)
- ✓ Methicillin-Resistant Staphylococcus aureus (MRSA)
- ✓ Escherichia coli (E. coli)
- ✓ Streptococcus pyogenes (S. pyogenes)
- ✓ Shigella dysenteriae (Shigella)
- ✓ Salmonella enteritidis (Salmonella)
- ✓ Pseudomonas aeruginosa (P. aeruginosa)

## SPECIFICATIONS

- Ozone and humidity process kills dangerous pathogens.
- Dimensions: 79 3/16" H x 52 5/8" W x 62" D.
- Capacity: 103 cu ft.
- Weight: 494 lbs.
- Connects to ordinary 120V NEMA 5-20R outlet on dedicated 20 amp circuit (see illustration).
- Power Consumption: 800 Watts during Sanitizing Cycle; 17 Watts during standby mode.
- Recommended maximum load of Refrigiwear insulated suits = 12 (6 per ZONO rack).
- Cycle Complete - Blue indicator light and buzzer. Manager can change from blue to yellow or white color and can disable buzzer with proper password.
- E-stop Button shield to prevent inadvertent disruption of cycle.
- Complies with NIOSH and OSHA safety & health standards.
- Complies with EPA's FIFRA standards for Pest Control Devices.



Requires NEMA 5-20R  
 120V Receptacle  
 Within 5 ft of the upper  
 right rear corner

## EASE OF USE FEATURES

- ERGONOMIC** Integrated Mobil Cart System alleviates the need for bending and lifting.
- FAST** Minimum cycle time - 38 minutes. The cycle will automatically be extended to raise humidity in machine if ambient humidity is below 50% and/or if item loaded are bulky and dry. Note: Start-up of cycle time may be extended to build-up humidity in the cabinet for optimum treatment efficacy. Density of users' items loaded in the cabinet and ambient humidity in the building will influence the potential for delay of start-up, if any.

## ACCESSORIES

**IGC** Industrial PPE Garmet Cart    **GC** Garment Cart    **4S UC** 4-shelf Utility Cart